

**MICRO SWITCH**FREEPORT ILLINOIS
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-3R**BZ-3R****M**DRAWING
NUMBER

ISSUE

13

PAGE 1 OF 1

REPLACES

RELEASE NO.

CHECK

REVISIONS

A CO17410

G C H
22 MAR 63

B CO31863

S R H
27 MAR 73

C CO 46304

R J H
21 NOV 79

D CO 58037

S M A
1 OCT 85E CO-
78874D L T
17 NOV 94

F CO93346

D L T
1 SEP 98G CO-
84234L J K
8 MAR 99

CHECK

26 MAR 63

CHECK

L.S.D

CHECK

22 MAR 63

CHECK

FORMTEK


FO-50378

DRAWN

G C H

22 MAR 63

CHECK



NOTE

△ - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE ----- 14 - 20 OZ	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE ----- 4 OZ MIN	UNDERWRITERS' LAB. INC. LISTED RATING 15A-125, 250 OR 480 VAC, 2A-600 VAC -L74- 1/8HP-125 VAC; 1/4HP-250 VAC 1/2A-125 VDC; 1/4A-250 VDC	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:
DIFFERENTIAL TRAVEL ----- .0008 - .0030	-L288-	ONE PLACE (.0) ± .030
OVERTRAVEL ----- .005 MIN	-L299- 16A 250V ~ T85 5E4	TWO PLACE (.00) ± .015
		THREE PLACE (.000) ± .005
		ANGLES ±
		WEIGHT .050 LB