
Part Number : 1300061435
Product Description : Mini-Change A-Size Single-Ended Cordset, 5 Poles, Male (Straight) to Pigtail, 16 AWG, Yellow PVC Cable, 0.91m (3.0') Length
Series Number : 130006
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : 105002A01F030



Documents and Resources

Drawings

1300061435_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead; diphenyl(2,4,6-trimethylbenzoyl)phosphine oxide per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	130006
Description	Mini-Change A-Size Single-Ended Cordset, 5 Poles, Male (Straight) to Pigtail, 16 AWG, Yellow PVC Cable, 0.91m (3.0') Length
IP Rating	IP67
Product Name	Mini-Change
Protocol	DeviceNet
Type	Single Ended
UPC	78678843404

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	600V

Physical

Cable Diameter	12.70mm (.500")
Cable Length	0.91m (3.0')
Color - Cable Jacket	Yellow
Connector End A	Mini-Change
Connector End B	Pigtail

Downloaded from Arrow.com.

Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	TPE
Material - Contact	Brass
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	142.000/g
Orientation	Straight to Pigtail
Poles	5
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	STOOW
Wire Size (AWG)	16

Downloaded from Arrow.com.