Part Number : 936030063
Product Description : Heavy-Duty Connector Kit, 10 Pole, Series S-E Female-Male Inserts, M20 Die-cast Aluminum Hood-Top Entry, Surface Mount Housing-Vertical, 2 Lever, Size 10B «57x27», Grey
Series Number : 93603
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Part Number : 7910.7765.0



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93603
Description	Heavy-Duty Connector Kit, 10 Pole, Series S-E Female-Male Inserts, M20 Die-cast Aluminum Hood-Top Entry, Surface Mount Housing-Vertical, 2 Lever, Size 10B «57x27», Grey
Component Type	Connector Kit - Female+Male
Insert Series	S-E
Kit Component Parts	Heavy-Duty Standard (STD) Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Top Entry, Size 10B «57x27», Extended M20 Thread, Grey, Heavy-Duty Screw Terminal Insert, Male, 10-Pole, 16A, with Wire Protection, Silver (Ag) Plated Contacts, Size 10B «57x27», Heavy-Duty Screw Terminal Insert, Female, 10-Pole, 16A, with Wire Protection, Silver (Ag) Plated Contacts, Size 10B «57x27», Heavy-Duty Standard (STD) Double Lever Surface Mount Housing, Die-cast Aluminum, with 2 Levers, with Gasket, Size 10B «57x27», M20 Thread, Grey
Product Name	Heavy-Duty Connectors
UPC	887191863610

Downloaded from Arrow.com.

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	500V

Physical

Component Size	10B «57X27»
Lock to Mating Part	Yes
Mounting Style	Surface Mount
Net Weight	506.000/g
Packaging Type	Bag
Thread Size	M20
Thread Type	(M) Metric

Kit Component Parts

Description	Part Number
Heavy-Duty Standard (STD) Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Top Entry, Size 10B «57x27», Extended M20 Thread, Grey	936011746
Heavy-Duty Screw Terminal Insert, Male, 10-Pole, 16A, with Wire Protection, Silver (Ag) Plated Contacts, Size 10B «57x27»	936010238
Heavy-Duty Screw Terminal Insert, Female, 10-Pole, 16A, with Wire Protection, Silver (Ag) Plated Contacts, Size 10B «57x27»	936010231
Heavy-Duty Standard (STD) Double Lever Surface Mount Housing, Die-cast Aluminum, with 2 Levers, with Gasket, Size 10B «57x27», M20 Thread, Grey	936011559

Downloaded from Arrow.com.