



Part Number : [1300980205](#)
Product Description : MAX-LOC Multi-Hole Strain Relief, 2, 3, 4, 5, 6, or 7 Hole Grommet, 1/2" NPT, Straight Male with O-Ring, Cable Diameter 4.75mm (.187")
Series Number : 130098
Status : Active
Product Category : Cable Grips
Engineering Number : 5594-008W



Documents & Resources

Drawings

[1300980205_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130098
Description	MAX-LOC Multi-Hole Strain Relief, 2, 3, 4, 5, 6, or 7 Hole Grommet, 1/2" NPT, Straight Male with O-Ring, Cable Diameter 4.75mm (.187")
Comments	Indicates that one or more grommet hole is covered by a thin membrane which can easily be "Poked" open if required.
NEMA Rating	NEMA 6P
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678818948

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	4.75mm (.187")
Color - Grommet	Yellow
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A

Mesh Length	N/A
Number of Holes	2, 3, 4, 5, 6, or 7
O-Ring	Yes
Thread Size	1/2" NPT

Mates With / Use With

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 1/2" NPT	<u>1300990143</u>

This document was generated on Sep 13, 2025