LOCKING DIN CABLE MOUNT



Male plug with ground key-rib. Unique 30° turn lockring securely fastens two halves of connector. Mates with lock flange female connectors and receptacles. Insert screw holds insert assembly in shell and also retains lockring on shell. Flexible black strain relief with 7/32" diameter cable entry. Heavy duty clamp.

Questions? Contact Switchcraft Customer Support at 1-773-792-2700

Product	Description	Stock
05CL3MX	DIN Cable Mount Connector, Male plug with ground key-rib, 3 pins at 180°	
05CL5MX	DIN Cable Mount Connector, Male plug with ground key-rib, 5 pins at 180°	
06EL5FX	DIN Cable Mount Connector, female plug with ground contact, 5 contacts at 180°	
09CL4MX	DIN Cable Mount Connector, Male plug with ground key-rib, 4 pins at 210°	
12CL5MX	DIN Cable Mount Connector, Male plug with ground key-rib, 5 pins at 240°	
13EL5FX	DIN Connector Receptacle, female plug with ground contact, 5 contacts at 240°	
15CL7MX	DIN Cable Mount Connector, Male plug with ground key-rib, 7 pins at 270°	
15CL8MX	DIN Cable Mount Connector, Male plug with ground key-rib, 8 pins at 270°	

Downloads:

Specification Sheet - Printer friendly version

Associated Products:



DIN Right Angle PC Mount Receptacles



Mini DIN Single Right Angle Receptacles SMD Series



DIN Panel Mount

Downloaded from Arrow.com.