Pushing Performance
Since 1945

M12-ACC-HOUSING



Image is for illustration purposes only. Please refer to product description.

Part number	21 41 000 0010
Specification	M12-ACC-HOUSING
HARTING eCatalogue	https://harting.com/21410000010

Identification

Category	Accessories
Series	Circular connectors M12
Type of accessory	Housing
Description of the accessory	for front mounting M14.5 x 1

Version

Gender	Female
Locking type	Screw locking
Details	If necessary, order lock nut 21 41 000 0011 separately.

Technical characteristics

Mounting height	9 mm
Tightening torque	1 Nm Lock nut
Degree of protection acc. to IEC 60529	IP67 mated condition

Material properties

RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Commercial data

Packaging size	25
Net weight	6.885 g
Country of origin	Slovakia
European customs tariff number	85389099
GTIN	5713140236516
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.