# Datasheet for part number MDM-37SCBRPT-F222

| Our Catalog Part Number: MDM-37SCBRPT-F222 |
|---|
| Our Global Manufacturing Part Number: 096521-2737 |
| Brand: Cannon Product Category: Micro Product Line: Micros Series: MICRO |

| Product Datasheet | |
|---|---|
| Series | MDM Micro D |
| Contact Quantity | 37 |
| Contact Gender | Socket |
| RoHS Compliant | Yes |
| Shell Style | Receptacle |
| Contact Material | Gold plated copper alloy |
| Contact Term Type | PC Tail |
| Contact Resistance | 8 milliohms max. |
| Termination Type | Right Angle Narrow Profile PCB |
| Wire Length | .109 (2.77) ±.015 (0.38) Standard |
| Shell Material | Metal Shell |
| Plating | Yellow Chromate/Cadmium over Nickel |
| Insulator Material | Contact size 9 to100 = liquid crystalline polymer, contact arrangements 7C2 or 24C4 = Diallyl phthalate |
| Hardware | Jackpost (standard) |
| PCB Hardware | Threaded insert |
| Coupling | Jackscrew Coupling |
| Current Rating | 3 A max. |
| Dielectric Withstanding Voltage | 600 VAC at sea level<br>150 VAC at 70,00' altitude |
| Insulator Resistance | 5000 megohms min. |
| Operating Temperature | -55°C to +200°C |
| Physical Shock | 50 G's, 3 axes, 6 milisecond duration sawtooth pulse |
| Vibration | 20G's, 10-2000 Hz. 12 hours |
| Durability | 500 cycles of mating and unmating, 500 CPH max. |
| Moisture Resistance | Insulator resistance > 100 megohms |
| SaltSpray | 48 hours |

Specifications and dimensions subject to change.



Downloaded from Arrow.com.