

Specification Sheet

Part Number: SRCI1000K2



Co-extruded hinge offers unlimited access to wire and cables and can be open and closed repeatedly without signs of wear.

Rubber based adhesive allows for a permanent bond to most surfaces.

TSR Adhesive Cable Clamp, 1.74" Width, 1" Height, PVC, Ivory, 50/pkg

Article Number	151-00280
Type	SRCI1000
Color	Ivory (IV)
Quantity Per	pack
Product Description	Manufactured from HellermannTyton's surface raceway, these adhesive cable clamps are designed with a co-extruded hinge offering unlimited and easy access to wire and cable. The clip can be open and closed repeatedly without deformation or signs of wear. The rubber based adhesive allows for a permanent bond to most surfaces. Available in three sizes.
Short Description	TSR Adhesive Cable Clamp, 1.74" Width, 1" Height, PVC, Ivory, 50/pkg
Global Part Name	SRCI1000-PVC-BGE

Length L (Imperial)	1.75
Length L (Metric)	44.45
Width W (Imperial)	1.88
Width W (Metric)	47.8
Bundle Diameter Max (Imperial)	1
Bundle Diameter Max (Metric)	25.4
Height H (Imperial)	1.0
Height H (Metric)	25.40
Material	Polyvinylchloride (PVC)
Material Shortcut	PVC
Adhesive	Rubber
Flammability	UL 94 V-0 (excluding adhesive)
UV Resistant (Yes/No)	No
Use Conditions	For Indoor Use Only
Operating Temperature	+122°F (+50°C)

Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)