

Specifications

Eaton DRA73-101-R

Eaton DRA inductor, 102 μ H, 0.682 A Irms, 0.763 A ISAT, 710 m Ω resistance, SMT mounting, Ferrite, 2-pins, 1350 qty.



Photo is representative



General specifications

PRODUCT NAME	Eaton DRA inductor
CATALOG NUMBER	DRA73-101-R
UPC	051712827928
PRODUCT LENGTH/DEPTH	7.6 mm
PRODUCT HEIGHT	3.55 mm
PRODUCT WIDTH	7.6 mm
PRODUCT WEIGHT	0.64 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	0.682 A
ISAT	0.763 A
PACKAGE QUANTITY	1350
MATERIAL	Ferrite
AUTOMOTIVE GRADE	Yes
CONTACT CONFIGURATION	Two-pads
TEMPERATURE RATING	-40 to 165 °C
RESISTANCE	710 mΩ
SIZE	7.5x7.5x3.4
TERMINALS	2 Pads
SERIES	DRA73

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - DRA73-101-R
	Eaton DRA automotive shielded drum core power inductors data sheet

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

