

Customer Information Sheet

DRAWING No.: R6372F02 / R6379F02 SHEET 2 OF 2	IF IN DOUBT - ASK	©	NOT TO SCALE	THIRD ANGLE PROJECTION	ALL DIMENSIONS IN mm





PART No.	L1
R6372F02	6.00
R6373F02	8.00
R6374F02	10.00
R6375F02	12.00
R6376F02	14.00
R6377F02	16.00
R6378F02	18.00
R6379F02	20.00

ORDER CODE:
R637XF02
LENGTH L1 IN mm
PLATING FINISH:
02 = NICKEL

CP	1	19.03.10	10711
NAME	ISS.	DATE	C/NOTE

APPROVED: C.PENROSE
CHECKED: R.ADDE
DRAWN: C.PENROSE
CUSTOMER REF.:
ASSEMBLY DRG:

NOTES:
1. FOR STANDARD PARTS SEE R30-100XXXX.

HARWIN

HARWIN USA
TEL: 603 893 5376
FAX: 603 893 5396
mis@harwin.com

HARWIN Europe (UK)
TEL: 023 9231 4545
FAX: 023 9231 4590
mis@harwin.co.uk

HARWIN Asia
TEL: +65 6 779 4909
FAX: +65 6 779 3868
mis@harwin.com.sg

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:
BRASS CW614N M
TO BS EN 12164

FINISH: SEE ABOVE

S/AREA: mm²

TITLE:
M3 HEXAGONAL
FEMALE SPACER

DRAWING NUMBER:
R6372F02 / R6379F02

SHT 2 OF 2