



Overview

Lead time	Usually in Stock
-----------	------------------

Physical

Colour	Beige
Depth	14.1 cm
Height	11.6 cm
Mounting preference	No preference
Net weight	3.1 kg
Mounting mode	Not rack-mountable
Width	21.4 cm

Input

Network frequency	47...63 Hz
Plug standard	IEC 60320 C14
Input voltage limits	160...290 V
Input voltage	230 V

Output

Rated power in W	600 W
Maximum configurable power in W	600 W
Output voltage	230 V
Rated power in VA	600 VA

Conformance

Product certifications	C-Tick CE GOST
Standards	EN 55024 EN 60950

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.00...15240.00 m

Batteries & Runtime

Number of battery filled slots	0
Number of battery free slots	0
Liquid value	0

Surge Protection and Filtering

Surge energy rate	300 J
-------------------	-------

Packing Units

Package 1 Weight	3.4 kg
Package 1 Height	17.5 cm
Package 1 width	27.3 cm
Package 1 Length	20.7 cm
SCC14	10731304197895
Number of Units in Package 2	4
Package 2 Weight	14.51 kg
Package 2 Length	424.94 mm
Number of Units in Package 3	64

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------