

USB 3.0 SuperSpeed Type-A Extension Cable (M/F), Black, 6-in. (15.24 cm)

MODEL NUMBER: **U324-06N-BK**



Extends your existing USB 3.0 connection by 6 in.

Features

Extend an Existing USB 3.0 Cable an Extra 6 in.

- Female USB-A connector attaches to current USB 3.0 cable

Enjoy SuperSpeed Transfer Rates in High-End Applications

- Supports data transfer rates up to 5 Gbps—10X the speed of USB 2.0
- Bi-directional interface allows data to flow both directions at the same time, increasing theoretical bandwidth by 10X

Premium Construction for Superior Signal Transfer

- Premium foil and braid shielding blocks EMI/RFI interference
- Molded nickel-plated connectors ensure excellent connectivity
- Integral strain relief for cable and connectors' long life
- Twisted 28/24 AWG data/power lines
- Rugged PVC jacket

Specifications

OVERVIEW	
UPC Code	037332193513
Technology	USB 3.0 (SuperSpeed); USB

Highlights

- Supports data transfer rates up to 5 Gbps
- Bi-directional interface allows data to flow both directions
- Backward compatible with previous USB generations
- Double-shielded protection against EMI/RFI
- Molded nickel-plated conductors

Package Includes

- U324-06N-BK USB 3.0 SuperSpeed Type-A Extension Cable (M/F), Black, 6 in.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Black
Cable Outer Diameter (OD)	5.5MM
Cable Jacket Rating	VW-1
Cable Length (ft.)	0.5
Cable Length (m)	0.2
Cable Length (in.)	6
Material of Construction	PVC
Cable Length (cm)	15.24
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.03
Shipping Weight (lbs.)	0.06
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-4 to 185 F (-20 to 85 C)
Relative Humidity	10% to 85%, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	USB 3.0 A (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps)
STANDARDS & COMPLIANCE	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>