
**Part Number :** 1300070113
**Product Description :** Mini-Change B-Size Single-Ended Cordset, 7 Poles, Male (Straight) to Pigtail, 16/7 AWG, Yellow PVC Cable, 0.91m (3.0') Length
**Series Number :** 130007
**Status :** Active
**Product Category :** Circular Industrial Cordsets
**Engineering Part Number :** 207002A01F030



## Documents and Resources

### Drawings

1300070113_sd.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Contains Lead; Di-(2-ethylhexyl)phthalat per ED/88/2018 (15 January 2019) |
| EU RoHS | Compliant with Exemption 6(c) per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Circular Industrial Cordsets |
| Series | 130007 |
| Description | Mini-Change B-Size Single-Ended Cordset, 7 Poles, Male (Straight) to Pigtail, 16/7 AWG, Yellow PVC Cable, 0.91m (3.0') Length |
| IP Rating | IP67 |
| Product Name | Mini-Change |
| Protocol | DeviceNet |
| Type | Single Ended |
| UPC | 78678844006 |

### Agency

| | |
|---|---|
| CSA | LR6837 |
| UL | E152210 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 8.0A |
| Voltage - Maximum | 600V |

### Physical

| | |
|---|---|
| Cable Diameter | 13.72mm (.540") |
| Cable Length | 0.91m (3.0') |
| Color - Cable Jacket | Yellow |
| Connector End A | Mini-Change |

Downloaded from Arrow.com.

| | |
|---|---|
| Connector End B | Pigtail |
| Coupling Style | Threaded |
| Gender | Male-Pigtail |
| Keyway | Single |
| LED Indicator | None |
| Material - Cable Jacket | PVC |
| Material - Connector Body | TPE |
| Material - Contact | Brass |
| Material - Coupling Nut | Black Epoxy Coated Zinc |
| Material - Plating Mating | Gold |
| Net Weight | 36.360/g |
| Orientation | Straight to Pigtail |
| Poles | 7 |
| Temperature Range - Operating | -20° to +105°C |
| Wire/Cable Type | STOOW |
| Wire Size (AWG) | 16 |



Downloaded from Arrow.com.