

FO converters - OPTOSUB-PLUS-K/OUT - 2799610

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



INTERBUS/fiber optic adapter, for converting the remote OUT interface to polymer/PCF fiber, connection system: F-SMA

The figure shows version
OPTOSUB-PLUS-G/OUT and
OPTOSUB-PLUS-K/OUT

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 129705
GTIN	4017918129705
Weight per Piece (excluding packing)	43.600 g
Custom tariff number	85176200
Country of origin	Germany

Technical data

Dimensions

Width	16.3 mm
Height	57 mm
Depth	31.3 mm

Ambient conditions

Ambient temperature (operation)	0 °C ... 55 °C
---------------------------------	----------------

General

Transmission channels	2 (1/1), Rx/D, Tx/D, full duplex
Net weight	30.68 g

FO converters - OPTOSUB-PLUS-K/OUT - 2799610

Technical data

General

Housing material	ABS, metal-plated
------------------	-------------------

Power supply

Nominal supply voltage	none, supply from data channel
Typical current consumption	typ. 30 mA

Interfaces

Interface 1	RS-485 interface INTERBUS in acc. with DIN 50254
Connection method	D-SUB 9 plug
Transmission medium	Copper
Serial transmission speed	500 kbps

Optical interface FO

Transmission power	354.81 μ W (-4.5 dBm at 980/1000 μ m)
	11.22 μ W (-19.5 dBm at 200/230 μ m)
Minimum receiver sensitivity	-26 dBm
Wavelength	660 nm
Transmission length incl. 3 dB system reserve	50 m (With F-P 980/1000 230 dB/km with quick mounting connector)
	300 m (with F-S 200/230 10 dB/km)
	100 m (F-S 200/230 10 dB/km, OPTOSUB/FO bus terminal module)
Transmission medium	Polymer fiber
	PCF fiber
Connection method	F-SMA

Conformance/approvals

Designation	EAC
Identification	EAC

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	19170132
eCl@ss 4.0	27230200
eCl@ss 4.1	27230200
eCl@ss 5.0	27230200
eCl@ss 5.1	27230200

FO converters - OPTOSUB-PLUS-K/OUT - 2799610

Classifications

eCl@ss

eCl@ss 6.0	19179200
eCl@ss 7.0	19179290
eCl@ss 9.0	19170114

ETIM

ETIM 2.0	EC001423
ETIM 3.0	EC001423
ETIM 4.0	EC001423
ETIM 6.0	EC001467
ETIM 7.0	EC001467

UNSPSC

UNSPSC 6.01	30211506
UNSPSC 7.0901	39121008
UNSPSC 11	39121008
UNSPSC 12.01	39121008
UNSPSC 13.2	43222604
UNSPSC 18.0	43223323
UNSPSC 19.0	43223323
UNSPSC 20.0	43223323
UNSPSC 21.0	43223323

Accessories

Accessories

Media converter

FO converters - OPTOSUB-PLUS-K/IN - 2799584



INTERBUS/fiber optic adapter, for converting the remote IN interface to polymer/PCF fiber, connection system: F-SMA

FO converters - OPTOSUB-PLUS-K/OUT - 2799610

Accessories

FO converters - OPTOSUB-PLUS-G/IN - 2799623



INTERBUS/fiber optic adapter, for converting the remote IN interface to fiberglass, connection system: B-FOC