

# HC-ALU 6-100,5 COVER GY - End cover



2200901

<https://www.phoenixcontact.com/us/products/2200901>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Profile housing, End cover, with screws and seal, for 100.5 mm profile width (internal), width: 124.4 mm, length: 15 mm, depth: 100.5 mm

## Your advantages

- Aluminum extruded profile
- Available in lengths from 100 mm ... 1000 mm, can be cut to any length
- Available in overall widths from 53.5 mm ... 161 mm
- Up to IP65 degree of protection
- Can be used as handheld and wall housing
- Optional EMC seals available

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2200901       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AC02          |
| Product key                          | ACFAAC        |
| GTIN                                 | 4046356716567 |
| Weight per piece (including packing) | 134.7 g       |
| Weight per piece (excluding packing) | 129.6 g       |
| Customs tariff number                | 76169910      |
| Country of origin                    | HU            |

# HC-ALU 6-100,5 COVER GY - End cover



2200901

<https://www.phoenixcontact.com/us/products/2200901>

## Technical data

### Product properties

|                              |                                                                        |
|------------------------------|------------------------------------------------------------------------|
| Product type                 | Panel mounting base side part                                          |
| Housing type                 | Profile housing                                                        |
| Housing series               | HC-ALU                                                                 |
| Product family               | HC-ALU 6-100,5                                                         |
| Type                         | End cover, with screws and seal, for 100.5 mm profile width (internal) |
| Ventilation openings present | no                                                                     |

### Dimensions

|        |          |
|--------|----------|
| Width  | 124.4 mm |
| Depth  | 100.5 mm |
| Length | 15 mm    |

### Material specifications

|                         |                          |
|-------------------------|--------------------------|
| Color (Housing)         | graphite grey (RAL 7024) |
| Surface characteristics | powder coated            |

### Environmental and real-life conditions

#### Ambient conditions

|                        |      |
|------------------------|------|
| Max. IP code to attain | IP65 |
|------------------------|------|

# HC-ALU 6-100,5 COVER GY - End cover



2200901

<https://www.phoenixcontact.com/us/products/2200901>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27190602 |
| ECLASS-15.0 | 27190602 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002779 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

# HC-ALU 6-100,5 COVER GY - End cover



2200901

<https://www.phoenixcontact.com/us/products/2200901>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)