



Search by part # or keyword

Products

Industries &
Solutions

Resources

TE Store

Sign In



Connectors > Power Connectors, Contacts, & Terminals > Circular Power > Circular Power Connectors

Purchase items directly
from TE.com

5-846290-1

LGH-4 SGL MOLDED END LEAD



LGH | LGH SGL

TE Internal #: **5-846290-1**

TE Internal Description: **LGH-4 SGL MOLDED
END LEAD**

Product Type : **Lead Assembly**

Operating Voltage (VDC): **50000**

Wire Size (AWG): **16**

Operating Temperature Range (°C): **-55 – 125**

Shielded : **No**

[Similar Products](#) | [Digital Datasheet](#)

Compatible Parts & Tooling

We are here to help!

Get in touch with our product experts.



CHAT WITH US



EMAIL US



CALL US

Documents

Features

Product Compliance

Product Drawings

LGH-4 SGL MOLDED END LEAD

[LGH-4 SGL MOLDED END LEAD](#) English

CAD Files

3D PDF

[3D_CVM_CVM_5-846290-1_AA.pdf](#) 3D

Customer View Model

[ENG_CVM_CVM_5-846290-1_AA.2d_dxf.zip](#)

English

[ENG_CVM_CVM_5-846290-1_AA.3d_igs.zip](#)

English

[ENG_CVM_CVM_5-846290-1_AA.3d_stp.zip](#)

English

Datasheets &
Catalog Pages

Products for Aerospace and Defense

[ENG_DS_1308940_Aerospace_Defense_0118.pdf](#)

English

Product
Specifications

Product Specification

[ENG_SS_108-36033_O2.pdf](#) English

Product
Environmental
Compliance

REACH Substance Communication Document

[ENG_PC_RSCD_Lead_1.pdf](#) English

Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.	
Product Type Features	Product Type : Lead Assembly
Electrical Characteristics	Operating Voltage (VDC): 50000
Dimensions	Wire Size (AWG): 16 Assembly Length : 304.8 mm [12 in] Pigtail Length : 9.65 mm [.38 in]
Usage Conditions	Operating Temperature Range (°C): -55 – 125 Shielded : No
Statement of Compliance	Statement of Compliance pdf

Products with Similar Specs

[View All Similar Products](#)

THIS PRODUCT

TOP RESULTS ?

CIRCULAR POWER CONNECTORS
5-846290-1
LGH-4 SGL MOLDED END LEAD



Non-Stocked

Product Type : **Lead Assembly**
Operating Voltage : **50000 VDC**
Wire Size : **16 AWG**
Operating Temperature Range : **-55 – 125 °C**
Shielded : **No**

CIRCULAR POWER CONNECTORS
1-5830637-2
LGH-1L SGL MLD END LEAD



Non-Stocked

Product Type : **Lead Assembly**
Operating Voltage : **25000 VDC**
Wire Size : **16 AWG**
Operating Temperature Range : **-55 – 125 °C**
Shielded : **No**

CIRCULAR POWER CONNECTORS
4-5830611-8
LGH 1/2 SNGL MLD END



Non-Stocked

Product Type : **Lead Assembly**
Operating Voltage : **10000 VDC**
Wire Size : **16 AWG**
Operating Temperature Range : **-55 – 125 °C**
Shielded : **No**

CIRCULAR POWER CONNECTORS
5-839564-1
LEAD, SGL END ASSY, LGH



Non-Stocked

Product Type : **Lead Assembly**
Operating Voltage : **30000 VDC**
Wire Size : **16 AWG**
Operating Temperature Range : **-55 – 125 °C**
Shielded : **No**

Also in the Series | [LGH SGL](#)



Circular Power
Connectors (306)

[ABOUT TE CONNECTIVITY](#)

[FOR PARTNERS](#)

[SUPPORT](#)

[CALL US](#)

[LIVE CHAT](#)

[UNITED STATES \(EN\)](#)