

Catalog

Home > Catalog



Home > 3048-C-440-B



Swage Standoffs

Model: 3048-C-440-B

Select Finish

-0 No Plate

Select Finish

-0 No Plate

Choose a CAD format

Product Details

These standoffs are made of Brass. They are Round shaped with diameter as 1/4". The thread for this part is 4-40 and length is 5/16".

SWAGE TOOLING

±.003	S	P
.075	A	1/32
.105	B	1/16
.135	C	3/32
.165	D	1/8
.230	E	3/16
.290	F	1/4

PDF Catalog

[RAF_catalog_0097.pdf](#)

Thread	4-40
O.D.	1/4"
Shape	Round
Length (L)	5/16"
Material	Brass
RoHS	Yes
Shank Length	0.135"
Board Thickness	3/32"
Shank Diameter	0.188"
Thread Clearance	0.150"
Finish	-0 No Plate



Technical Information

[Electronic Hardware Components](#)

[Engineering Data](#)

[Capabilities Brochure](#)

[Services](#)

[Distributors](#)

Company

[RAF Quality Management](#)

[Industry Links](#)

[What's New](#)

[News](#)


[About](#)

[Contact](#)

[Careers](#)

Contact Us

Find Us



95 Silvermine Rd.
Seymour CT 06483

Downloaded from [Arrow.com](#)