



**Part Number :** [190700015](#)

**Product Description :** InsulKrimp Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 10 (M5), Length 22.00mm, Red, Carton

**Series Number :** 19070

**Status :** Active

**Product Category :** Ring and Spade Terminals

**Engineering Part Number :** AA-221-10X

---

## Documents and Resources

### Drawings

[190700015 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications


[PS-19902-009-001.pdf](#)

[PS-19902-013-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Ring and Spade Terminals
Series	19070
Description	InsulKrimp Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 10 (M5), Length 22.00mm, Red, Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	InsulKrimp
Style	Ring
Type	Ring Terminal, Metric Ring Terminal
UPC	800753068780

### Agency

CSA	LR18689
UL	E32244

### Physical

Barrel Type	Closed
Color - Resin	Red

Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin
Net Weight	0.617/g
Packaging Type	Carton
Stud Size	10 (M5)
Wire Insulation Diameter	3.70mm max.
Wire Size (AWG)	18, 20, 22
Wire Size mm <sup>2</sup>	0.35-0.80

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Application Tooling

### Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 22-10 AWG and 6.0-0.5mm <sup>2</sup> (Rings, Spades, Hooks, Block Spades and Flanged Spades)	<a href="#"><u>640010100</u></a>
PremiumGrade Hand Crimp Tool for Insulkrimp Terminals and Splices, 22-10 AWG (Rings, Spades, Hooks, Block Spades and Flanged Spades)	<a href="#"><u>640010300</u></a>
Crimp Head for the AT-200 Pneumatic Hand Tool	<a href="#"><u>640050100</u></a>
Crimp Head for the AT-200 Pneumatic Hand Tool	<a href="#"><u>640050300</u></a>
ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	<a href="#"><u>640160036</u></a>

---

This document was generated on May 20, 2026