





APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/25/16	

**SPECIFICATIONS:****Material:**

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

15u" Gold over Nickel underplate on contact area,  
Tin over Nickel underplate on tails.**Electrical:**

Current rating: 2.0 Amp

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 500 VAC/DC for 1 minute

**Temperature Rating:**

Operating temperature: -40°C to +105°C

**Environmental:**

Lead free, RoHS compliant.

**RoHS**  
COMPLIANT

Positions: 8, 10, 14, 16, 20, 24, 26, 30, 34, 40, 44, 50  
 A = .079 [2.00] X No. of Positions per row + .033 [0.85]  
 B = .079 [2.00] X No. of Spaces per row  
 C = .079 [2.00] X No. of Positions per row + .104 [2.65]  
 D = .079 [2.00] X No. of Positions per row + .039 [1.00]

UNLESS OTHERWISE SPECIFIED  
 ALL DIMENSIONS ARE INCHES [MM]  
 TOLERANCES: EXCEPT AS NOTED  
 INCHES HOLES  
 .X ± .10 ØX ± .10  
 .XX ± .020 ØXX ± .015  
 .XXX ± .015 ØXXX ± .010

APPROVALS DATE

DRAWN AY 3/25/16

CHECKED MY 3/25/16

APPROVED \_\_\_\_\_

**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

.079 [2.00] BOX HEADER, DUAL ROW,  
 RIGHT ANGLE, 15u" SEL GOLD PLATED

SIZE

PART NO.

REV.

X

2BHR-A2-XX-HSGA-SS-15

-

REF:

S00019C

SCALE: NTS

SHEET 1 OF 1