

SDIS 0.8X4.0X100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com 1000 V
IEC 60900

VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1.
SoftFinish grip

General ordering data

Version	Screwdriver, Screwdriver
Order No.	9008400000
Type	SDIS 0.8X4.0X100
GTIN (EAN)	403224805636 1
Qty.	1 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2021-06-30
Alternative product	2749820000

Creation date September 23, 2022 8:07:23 PM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

SDIS 0.8X4.0X100**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Width	210 mm	Width (inches)	8.268 inch
Diameter	30 mm	Net weight	56.445 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data

Description of article	VDE-insulated screwdriver with slotted blade 0.8x4.0x100
------------------------	--

Screwing tools

Blade length	100 mm	Blade thickness (A)	0.8 mm
Blade type	B	Blade width (B)	4 mm
Form	Slotted		

Classifications

ETIM 6.0	EC000158	ETIM 7.0	EC000158
ETIM 8.0	EC000158	ECLASS 9.0	21-04-04-07
ECLASS 9.1	21-04-04-07	ECLASS 10.0	21-04-04-07
ECLASS 11.0	21-04-04-07	ECLASS 12.0	21-04-04-07

Approvals

Approvals

**Downloads**

Approval/Certificate/Document of Conformity	Manufacturer's Declaration - Screwdrivers Declaration of the Manufacturer
Catalogues	Catalogues in PDF-format
Brochures	