



Part Number : [190230003](#)

Product Description : InsulKrimp Fully Insulated Quick Disconnect, Male, for 22-18 AWG (0.80-0.35mm²) Wire, Tab 4.75 x 0.51mm, Carton

Series Number : 19023

Status : Active

Product Category : Quick Disconnects

Engineering Part Number : AMCT-27X



Documents and Resources

Drawings

[190230003_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


Specifications

[PS-19902-008-001.pdf](#)

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19023
Description	InsulKrimp Fully Insulated Quick Disconnect, Male, for 22-18 AWG (0.80-0.35mm ²) Wire, Tab 4.75 x 0.51mm, Carton
Comments	Funnel Entry
Product Name	InsulKrimp
Type	Standard Quick Disconnect
UPC	800753039797

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
-------------	--------

Color - Resin	Red
Flammability	94V-0
Gender	Male
Glow-Wire Capable	No
Insulated	Partial
Insulation	PVC
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Zinc Chromate
Material - Plating Termination	Zinc Chromate
Net Weight	0.610/g
Orientation	Straight
Packaging Type	Carton
Polarized to Mating Part	No
Tab Thickness	0.51mm
Tab Width	4.75mm
Temperature Range - Operating	-50° to +105°C
Wire Insulation Diameter	3.70mm max.
Wire Size (AWG)	18, 20, 22

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Hand Crimp Tool	<u>640012400</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640052400</u>

This document was generated on Jan 05, 2026