

YAV8CL4, Uninsulated Ring Terminal For 8 AWG

By Burndy
Catalog # [YAV8CL4](#)

Copper Compression Lug, Heavy Duty, Ring Tongue, 1 Hole w/ Inspection Window, AN 8 Flex, 1/2" Stud, Short Barrel, Tin Plated



Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Application

Industrials, Hospitals, Utilities, Marine, Computer

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • Military Specified (Mil-Spec)
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Str Size	8
Conductor - Copper Str Aircraft Size	AN 8
Conductor Size	8 AWG
Conductor - Copper Str Size Range	8 AWG

Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size
----------------	--

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Pad Width inch	0.73 in
Package Height	0.000 in
Dimension - Stud Size inch	1/2
Dimension - B Length fraction	2/5 in
Dimension - B Length inch	0.41 in
Dimension - Z inch	0.48 in
Dimension - Bolt Size fraction	1/2
Dimension - Length Overall inch	1.52 in
Dimension - N inch	0.38 in

General

Die Index	38
Trade Name	HYLUG™
Material Composition	<ul style="list-style-type: none"> • DLP Copper • Tin Plating
Military Specification	AS20659
Sub Brand	HYLUG
Physical Attribute - Tongue Type	Ring
Application - For Use On	Copper Commercial (Code) Cable, Type AN Aircraft Cable, Extra Flexible Conductors
Plated	Y
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Type	Ring Tongue
UPC 14 Digit GTIN	00781810025130
Material	Copper
Plating Type	Tin
UPC	781810025130

Logistics

Minimum Pack Quantity 200
Carton Quantity 200
Pallet Quantity 99999

Product Assets

[Catalog \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
BRDY-YAV8CL4-SPEC-EN | REV 4/2026