

**Partlist****Search in the partlist [Devices]**

Search products by..

if necessary restrict the search on parts

20 70 305 3921**ESC 67-10 TP05, M12 D-Coding**

Series	Ethernet Switch ESC 67-10 TP05U HARTING RJ Industrial® IP 67 Data 3A Ethernet Switch for the industrial applications IP 65 / IP 67
Protection level	IP 65 / IP 67
Hood type	Robust metal housing of zinc die cast
Dimensions	45x120x87 (WxDxH in mm, without connector)
Mounting	35 mm standard rail acc. to DIN EN 60 715 Panel mounting fixation for upright assembly Panel mounting fixation for flat assembly
Operating temperature	-40 °C ... + 70 °C
Input voltage	24 V DC (18 ... 30 V DC)
Supply current	100 mA (at 24 V DC)
Terminals	compatible with Han® 4A connectors redundant power supply
Data transmission rate	10 or 100 MBit/s / auto-negotiation
Cables	Shielded Twisted Pair (STP) or Unshielded-Twisted-Pair (UTP), Category 5
Ethernet Interface available device	HARTING RJ Industrial® Data 3A connectors auto-crossing function
Max. cable length	100 m (Cat. 5) in acc. with EN 50 173

Inquiry© Copyright 1999-2006 Harting KGaA and its licensors - Any suggestions and bug reports are welcome at: HARKIS@harting.com