



Representative Image

Catalog No. TC106

Description: RIGHT ANGLE MNTG BRKT 1X1IN NAT NYL

UPC No 786210822501

Home > Wire & Cable Management > Ty-Rap > Cable tie mounts

Right-Angle Bundle Support, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 25.4mm (1.0 Inches), Width of 19.1mm (0.75 Inches), Height of 25.4mm (1.0 Inches), Two Screw Mounting Method, #4 Screw, Mounting Hole Size of 3.3mm (0.130 Inches)

Descriptors

Category	Cable tie mounts
Special Features	This style meets Military Specification requirements as a support at holes in bulkheads and walls.

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

Classifications

Brand Name	Ty-Rap
------------	--------

Dimensions

Mount Size	#4
------------	----

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000449 Mounting base and -element for cable ties
Length	25.4 mm
Length	1 inch
Width	19.1 mm
Width	0.75 inch
Height	25.4 mm
Height	1 inch

by ABB

ETIM	EC000449 Mounting base and -element for cable ties
Type of fastening	Other
Diameter mounting hole	3.3 mm
Material	Plastic
Material quality	Polyamide (PA)
Colour	Natural colour