


T 3376 500 U

Description	Male panel connector 5 pole IP40; solder; silver; bayonet locking
IP-class mated	IP40
number of positions (w/o PE)	5
rated current (40 °C)	5 (A)
rated voltage	300 (V)


active

Please log in to receive your price.

2,07 €
price

Total price
207,00 €
Your net plus VAT

100	pcs.

The minimum order amount is 100 pcs.; packing unit 100 pcs.
This product is currently not in stock.

add to cart

add to favorite

send request

Technical data | Downloads

General Characteristics		
contact diameter		1,5 mm
gender		male
termination		solder pin
Further Characteristics		
max. wire gauge		0.5
min. wire gauge		0.05
RoHS Compliant Yes		X
Electrical Characteristics		
rated current (40 °C)	(A)	5
rated voltage	(V)	300

Matching contacts



This website uses cookies.

We use cookies to provide you with a better service while you visit our website and also to adapt our range of services to your needs.
These cookies are used for technical, statistical and marketing purposes.
Please decide for yourself which types of cookies should be set when using our website. The types of cookies we use are described below under "Details". For further information please refer to our privacy policy.

Imprint - Data protection

Required | Statistics | Marketing | Details

Select Cookies | Accept Cookies

Downloaded from Arrow.com.