



Fig. 1




TNC Right Angle PCB Receptacle
31-5607

Fig. 2



TNC Right Angle PCB Receptacle
31-5660

Fig. 3



TNC Vertical PCB Receptacle
31-71063

TNC PRINTED CIRCUIT BOARD RECEPTACLES

Description	Dimensions, inches (millimeters)			Notes		Amphenol Number	Fig.
	a	b	d	Pit.	Ins.		
TNC Right Angle Printed Circuit Board Receptacle	.657 (16.7)	.642 (16.3)	1.366 (34.7)	P36/P27	D1	31-5607	1
TNC Right Angle Printed Circuit Board Receptacle	.756 (19.2)	.580 (14.7)	1.500 (38.1)	P6	D1/31	31-5660	2
TNC Vertical Printed Circuit Board Receptacle	.880(22.4)	.438 (11.1)	—	P15	D1	31-71063	3

▲ distributor stocked