Specifications







Eaton CLH1110R1-3-R050-R

Eaton CLH1110R inductor, 6-pins, 0.23 mΩ, Six, SMT, Three-phase, 25 A, 50 nH, 300, Ferrite

General specifications	
PRODUCT NAME	Eaton CLH1110R inductor
CATALOG NUMBER	CLH1110R1-3-R050-R
UPC	051712740746
PRODUCT LENGTH/DEPTH	22.5 mm
PRODUCT HEIGHT	10 mm
PRODUCT WIDTH	11 mm
PRODUCT WEIGHT	10.9 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

TYPE	Inductor
MOUNTING	SMT
PHASE	Three-phase
ISAT	25 A
PACKAGE QUANTITY	300
MATERIAL	Ferrite
CONTACT CONFIGURATION	Six-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	0.23 mΩ
TERMINALS	Six
INDUCTANCE	50 nH
SERIES	CLH1110R

Resources

SPECIFICATIONS AND DATASHEETS	Eaton CLH1110 multi phase inductor data sheet Eaton Specification Sheet - CLH1110R1-3-R050-R

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.