

Specification Sheet

Part Number: 133-02810



All-in-one bundling and fastening solution reduces costs and assembly time.

Anti-rotational oval fastener forces bundle to travel in intended direction.

1-Piece Cable Tie with Oval Fir Tree Mount, 6.2"L, 7.0 x 12.0 mm Hole Dia, PA66HIRHS, Gray, 2000/ctn

Article Number	133-02810
Type	T50SOSFT7X12
Color	Gray (GY)
Quantity Per	carton
Product Description	One-piece cable tie and mount offers a simple bundling and mounting solution. The disc feature prevents rattling in high-vibration applications and protects against debris ingress.
Short Description	1-Piece Cable Tie with Oval Fir Tree Mount, 6.2"L, 7.0 x 12.0 mm Hole Dia, PA66HIRHS, Gray, 2000/ctn
Global Part Name	T50SOSFT7X12-PA66HIRHS-GY

Minimum Tensile Strength (Imperial)	50
Minimum Tensile Strength (Metric)	222
Length L (Imperial)	6.2
Length L (Metric)	157.0
Fixation Method	Fir tree for round holes
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.19
Width W (Metric)	4.8
Bundle Diameter Min (Imperial)	0.08
Bundle Diameter Min (Metric)	2.0
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Thickness T (Imperial)	0.05
Thickness T (Metric)	1.3

Height H (Imperial)	0.58
Height H (Metric)	14.8
Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.57
Panel Thickness Min (Metric)	0.8
Panel Thickness Max (Metric)	14.5
Mounting Hole Diameter D (Imperial)	0.28 - 0.47 "
Mounting Hole Diameter D (Metric)	7.0 x 12.0 mm
Mounting Hole Diameter D Min (Imperial)	0.28
Mounting Hole Diameter D Max (Imperial)	0.47
Mounting Hole Diameter D Max (Metric)	12.0
Disc Diameter (Metric)	16.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS

Use Conditions	For Indoor Use Only
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)