
**Part Number :** 22012117
**Product Description :** KK 254 Crimp Housing, Friction Ramp, 11 Circuit
**Series Number :** 2695
**Status :** Active
**Product Category :** Connector Housings
**Engineering Part Number :** 2695-11R



## Documents and Resources

### Drawings

022012117_sd.pdf

26950002-PK-000.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

### Specifications

PS-10-07-001.pdf

TS-10-07-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Connector Housings |
| Series | 2695 |
| Description | KK 254 Crimp Housing, Friction Ramp, 11 Circuit |
| Application | Wire-to-Board |
| Component Type | Receptacle |
| Product Name | KK 254 |
| UPC | 800753689992 |

### Agency

| | |
|---|---|
| CSA | LR19980 |
| UL | E29179 |

### Physical

| | |
|---|---|
| Circuits (maximum) | 11 |
| Color - Resin | Natural (White) |
| Flammability | 94V-0 |
| Gender | Receptacle |
| Glow-Wire Capable | No |
| Lock to Mating Part | Yes |
| Material - Resin | Nylon |
| Net Weight | 1.169/g |
| Number of Rows | 1 |

Downloaded from Arrow.com.

| | |
|---|---|
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 2.54mm |
| Pitch - Termination Interface | 2.54mm |
| Stackable | No |
| Temperature Range - Operating | See Product Specification |

### Solder Process Data

| | |
|---|---|
| Lead-Free Process Capability | N/A |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| KK 254 RPC Vertical Headers with Friction Lock | 171856 |
| KK 254 RPC Right-Angle Headers with Friction Lock | 171857 |
| KK 254 Single Row Vertical Headers | 4030 |
| KK 254 Vertical Breakaway Headers with Friction Lock | 42375 |
| KK 254 Right-Angle Breakaway Headers | 42376 |
| KK 254 Right-Angle Surface Mount Compatible Breakaway Headers | 42377 |
| KK 254 Vertical Single Row Solid Headers | 6373 |
| KK 254 Vertical Single Row Headers | 6410 |

### Use with Part(s)

| Description | Part Number |
|---|---|
| Pre-Crimped Lead KK 254 Female-to-KK 254 Female, Tin (Sn) Plating, 150.00mm Length, 22 AWG, Black | 797580007 |

Downloaded from Arrow.com.

| | |
|---|---|
| Pre-Crimped Lead KK 254 Female-to-KK 254 Female, Tin (Sn) Plating, 300.00mm Length, 22 AWG, Black | 797580015 |
| KK 254 Female Crimp Terminals | 2759 |
| KK 254 Cat Ear Crimp Terminals | 41572 |
| KK 254 Female Crimp Terminals | 4809 |
| KK 254 Female Crimp Terminals | 6459 |
| KK 254 Female Crimp Terminals | 8088 |



Downloaded from Arrow.com.