



E32-T16W 2M

Fiber optic sensor head, through-beam, square, top-view, 30 mm area detection, R10 fiber, 2 m cable

Specifications

Sensing method	Through-beam
Sensing height	30 mm
Sensing distance	4000 mm
Cable length	2 m
Free cut	✓
Material core	Plastic
Degree of protection (IP)	IP50
Sensing surface orientation	Top-view
Shape	Square
Material sheath	PVC

Fits to



E3NX-FA41 2M

Fiber amplifier, twin digital display, smart tuning, PNP, single output, 2 m cable

CAD Library



Fiber Optic Sensors Group Catalogue

EN PDF 7.54 MB