




OBSOLETE

1.27 μm Au Min. (See note 4)

Hole data
scale 5:1



www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 										
			TOLERANCES UNLESS OTHERWISE SPECIFIED																
Dr	D.ANDREWS	93/06/25	ANGULAR		LINEAR		0.X		±0.1										
Eng	D.Andrews	93/06/25					0.XX		±0.1										
Chr	H.Bouwknegt	93/08/20					0.XX ±2		±0.1										
Appr	D.Andrews	93/08/20	Product family					METRAL		Spec ref -									
			title Mini Coax MALE PRESS-FIT TO B.P.					dwg no 88978		Rev G									
												catalog no		-		CUSTOMER		sheet 1 of 1	