





20極（参考）
20 CIRCUITS



基板穴推奨寸法（部品実装側）
RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE)

(SCALE:4-1)

注記 NOTE

1. 嵌合相手：51089-**05
   MATE WITH : 51089-**05

△2 イジェクターが開いた状態の寸法を示す。
EJECTORS IN OPEN POSITION.

△3 公差非累積
TOLERANCES : NON CUMULATIVE

部品 PART	材料 MATERIAL
ハウジング HOUSING	ポリエステル(PBT)、ガラス充填、UL 94V-0、色：グレー POLYESTER(PBT), GLASS FILLED, UL 94V-0, COLOR:GRAY
イジェクター EJECTOR	ポリエステル(PBT)、ガラス充填、UL 94V-0、色：グレー POLYESTER(PBT), GLASS FILLED, UL 94V-0, COLOR:GRAY
ピン PIN	黄銅 BRASS
	金めっき：0.5μmMIN. GOLD PLATING： 0.5μmMIN.
	ニッケルめっき(下地)：1.0～1.5μm NICKEL(UNDER PLATING)：1.0～1.5μm

DOCUMENT STATUS	P1	RELEASE DATE	2018/10/16 09:02:14

E	(D)	C	B	(A)	オーダー番号 ORDER NUMBER	極数 CKT
46.1	80.4	71.4	63.6	58	55458 6005	60
36.1	70.4	61.4	53.6	48	55458 5005	50
26.1	60.4	51.4	43.6	38	55458 4005	40
20.1	54.4	45.4	37.6	32	55458 3405	34
16.1	50.4	41.4	33.6	28	55458 3005	30
6.1	40.4	31.4	23.6	18	55458 2005	20

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS	SCALE
mm	NTS

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL	±	3.0 °
4 PLACES	±	0.2
3 PLACES	±	0.2
2 PLACES	±	0.2
1 PLACE	±	0.2
0 PLACES	±	0.2

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC:

EC NO: 605860
DRWN: RWATANABE01 2018/10/09
CHK'D: KOMURAKAMI 2018/10/16
APPR: TKANEKO 2018/10/16

INITIAL REVISION:
DRWN: RWATANABE01 2018/10/09
APPR: TKANEKO 2018/10/16

THIRD ANGLE PROJECTION | DRAWING: A3-SIZE | SERIES: 55458

molex

MI II 2.0 W/B DUAL ROW HEADER ASSY WITH EJECTOR

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
554580000-SD	PSD	000	A

MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
SEE CHART	GENERAL	1 OF 1

Downloaded from Arrow.com.