



Part Number : [191210007](#)

Product Description : InsulKrimp Flanged Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 8 (M4), Carton

Series Number : 19121

Status : Active

Product Category : Ring and Spade Terminals

Engineering Part Number : AA-215-08X



Documents and Resources

Drawings

[191210007_sd.pdf](#)

[PK-19902-001-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


Specifications

[PS-19902-009-001.pdf](#)

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS |  per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|--------------|---|
| Status | Active |
| Category | Ring and Spade Terminals |
| Series | 19121 |
| Description | InsulKrimp Flanged Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 8 (M4), Carton |
| Keyword | Spade Terminal, Spade Terminals |
| Product Name | InsulKrimp |
| Style | Spade |
| Type | Spade Connector, Metric Spade Connector |
| UPC | 800753095250 |

Agency

| | |
|-----|---------|
| CSA | LR18689 |
| UL | E32244 |

Physical

| | |
|--------------|--------|
| Barrel Type | Closed |
| Flammability | 94V-0 |

| | |
|---------------------------|------------|
| Insulation | PVC |
| Material - Plating Mating | Tin |
| Net Weight | 0.626/g |
| Packaging Type | Carton |
| Stud Size | 8 (M4) |
| Wire Insulation Diameter | 3.68mm |
| Wire Size (AWG) | 18, 20, 22 |
| Wire Size mm ² | 0.25-1.50 |

Solder Process Data

| | |
|------------------------------|-----|
| Lead-Free Process Capability | N/A |
|------------------------------|-----|

Application Tooling

Global

| Description | Part Number |
|--|------------------|
| PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 22-10 AWG and 6.0-0.5mm ² (Rings, Spades, Hooks, Block Spades and Flanged Spades) | <u>640010100</u> |
| PremiumGrade Hand Crimp Tool for Insulkrimp Terminals and Splices, 22-10 AWG (Rings, Spades, Hooks, Block Spades and Flanged Spades) | <u>640010300</u> |
| ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool | <u>640160036</u> |

This document was generated on Apr 27, 2026