

Products / Embedded Computing / Industrial Flash & Memory Solutions / Industrial Memory / SQR-SD3I /

SQR-SD3I

SODIMM DDR3L 1333/1600/1866 with Thermal Sensor (-40~85oC)

New



- 30u" golden finger
- Operating Temperature: -40° C to +85° C
- 100% Screening Test
- Original chip vendor adopted
- EEPROM with Thermal sensor
- Reliability/compatibility test by in-house testing/ 12hr Burn-In Test

Datasheet (PDF)

Documents & Downloads

*JEDEC standard 1.35V power supply
*JEDEC standard 204-pin Dual In-Line Memory Module [More](#)



Product Specifications (8)

[Download Spec](#)

Part Number			
Details			
	SQR-SD3I-1G1333SN	SQR-SD3I-2G1333SN	SQR-SD3I-2G1K3SNLB
Memory			
Advanced Feature			
Capacity			
Chip Manufacturer			
Chip Organization			
EOL			
Interface			
Manufacturer			
Operating Temperature			
PCB Height			
Rank			

RoHS Status		
Speed		
N/A	N/A	-
1GB	2GB	-
SAMSUNG	SAMSUNG	-
128M X 8	256M X 8	-
Phased-out	Phased-out	-
204Pin	204Pin	-
Advantech	Advantech	-
-40 - 85C	-40 - 85C	-
1.181"	1.181"	-
1 Rank	-	-
Yes	Yes	-
1333Mb/s	1333Mb/s	-
SGRAM		
Category		
Clock Speed		
Capacity		
Voltage		
Pins/DIMM		
Gold plating on PCB		
Operational Temperature		
Dimensions(mm)		
-	-	DDR3
-	-	1333 Mbps
-	-	2 GB
-	-	1.35V / 1.5V
-	-	204-Pin SODIMM
-	-	30μ
-	-	-40 ~ 85 °C
-	-	67.6 x 30

Support

[Datasheet \(PDF\)](#)

[Documents & Downloads](#)

Need more info? Talk to our Online Rep!

Live Chat

Inquiry Form

Related Materials

Catalog (1)

2016-2017 Embedded Computing
Product Catalog

6/17/2016 | Catalog

How Can We Help?



Buy Online



Support



Live Chat



1-888-576-9668



- Company Information
- Investor Relations
- Contact Us
- Corporate Citizenship (CSR)
- Global Exhibitions
- Careers