




A  
B  
C  
D

1 2 3 4

GENERAL CHARACTERISTICS and RoHS INFORMATION


see drawing C01-8639-0003



P/N LEAD FREE

|                  |            |
|------------------|------------|
| DAV11W1S500G00LF | UNC 4.40   |
| PART NUMBER      | Threaded A |

LAYOUT DIMENSIONS (after plating)  
CONNECTOR SIDE VIEW



| rev | ecn no    | dr  | date       |
|-----|-----------|-----|------------|
| A   | LS08-0012 | MPE | 2008/01/16 |
| -   | -         | -   | -          |
| -   | -         | -   | -          |
| -   | -         | -   | -          |
| -   | -         | -   | -          |
| -   | -         | -   | -          |

|                    |          |                                       |                                   |                       |               |
|--------------------|----------|---------------------------------------|-----------------------------------|-----------------------|---------------|
| www.fciconnect.com |          | surface<br>ISO 1302                   | tolerance std<br>ISO 406 ISO 1101 | projection            | mm            |
|                    |          | TOLERANCES UNLESS OTHERWISE SPECIFIED |                                   |                       | A3            |
| Dr                 | M PESSON | 2008/01/16                            | ANGULAR                           |                       |               |
| Eng                | PESSON   | 2008/01/16                            | LINEAR                            |                       |               |
| Chr                | LEGARE   | 2008/01/16                            | 0.XX' ±2°                         | 0.X                   | ±0.1          |
| Appr               | LEGARE   | 2008/01/16                            |                                   | 0.XX                  | ±0.1          |
|                    |          | Product family                        | D-SUB                             |                       | ECN LS08-0012 |
|                    |          |                                       |                                   | Spec ref              | -             |
| FCi                |          | SOCKET CONNECTOR 11W1 RA              |                                   | dwg no                | C-8639-2355   |
|                    |          | WITHOUT POWERS CONTACTS               |                                   | Rev.                  | A             |
|                    |          | catalog no                            | -                                 | CUSTOMER sheet 1 of 1 |               |