

Data Sheet | Item Number: 806-905


THT pin strip; straight; Pin spacing 5 mm; 5-pole; black

<https://www.wago.com/806-905>



Color: ■ black

Similar to illustration



Dimensions in mm

$L = (\text{pole no.} - 1) \times \text{pin spacing} + 4.8 \text{ mm}$

Connection Data

Number of levels 1

Connection 1

Pole number 5

Physical data

Pin spacing	5 mm / 0.197 inches
Width	24.8 mm / 0.976 inches
Height	12 mm / 0.472 inches
Depth	2.7 mm / 0.106 inches
Solder pin length	3.4 mm
Solder pin diameter	1 mm
Drilled hole diameter	1.3 (+0.05) mm

Mechanical data

Suitable Pin spacing: 5 mm / 0.197 inch

Plug-in connection

Contact type (pluggable connector)	Male connector/plug
Connector (connection type)	for PCB
Mating direction to the PCB	90°

PCB contact

PCB contact	THT
-------------	-----

Material data

Note (material data)	Information on material specifications can be found here
Color	black
Insulation material (main housing)	Polyamide (PA46)
Flammability class per UL94	V2
Fire load	0 MJ
Weight	0.7 g

Commercial data

Product Group	4 (Printed Circuit Connectors)
PU (SPU)	100 pcs
Packaging type	Box
Country of origin	DE
GTIN	4044918325882
Customs tariff number	85366930000

Product Classification

UNSPSC	39121409
eCl@ss 10.0	27-14-11-92
eCl@ss 9.0	27-14-11-92
ETIM 9.0	EC002848
ETIM 10.0	EC002848
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Downloads

Environmental Product Compliance


Compliance Search

Environmental Product
Compliance 806-905



Documentation

Additional Information

Technical Section	03.04.2019	pdf 2027.26 KB	
-------------------	------------	-------------------	---

CAD/CAE-Data

CAD data

2D/3D Models 806-905



CAE data

EPLAN Data Portal
806-905



PCB Design

Symbol and Footprint via
SamacSys 806-905



Symbol and Footprint via
Ultra Librarian 806-905

