Part Number : 1300940498
Product Description : Bus-Drop Support Grip, Single "U" Eye, Cable Diameter 17.78-21.59mm (.700-.850"), Approximate Break Strength 861.83kg (1900 lbs) , Stainless Steel
Series Number : 130094
Status : Active
Product Category : Cable Grips
Engineering Part Number : 36569SS



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130094
Description	Bus-Drop Support Grip, Single "U" Eye, Cable Diameter 17.78-21.59mm (.700-.850"), Approximate Break Strength 861.83kg (1900 lbs) , Stainless Steel
Product Name	Bus-Drop
Type	Support Grip
UPC	78678810322

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	861.83kg (1900 lbs)
Bale Length	0.229m (9.00")
Body Style	Straight
Cable Diameter	17.78-21.59mm (.700-.850")
Color - Grommet	N/A
Eye Type	Single
Gender	N/A
Material - Body	N/A
Material - Grip	Stainless Steel
Mesh Length	0.216m (8.50")
Net Weight	43.608/g
Number of Holes	N/A

Downloaded from Arrow.com.

O-Ring	No
Thread Size	N/A

Downloaded from Arrow.com.