



[CONNECTORS](#)

[CONNECTOR HOUSINGS](#)



✓ Active

TE CONNECTIVITY (TE)

1X4 GENERATION Y ASSY KEYA CPA

Generation Y Connector System

2035360-2

TE Internal Number: 2035360-2

[EU RoHS Compliant](#)

[EU ELV Compliant](#)

Connector System Wire-to-Board, Wire-to-Device, Wire-to-Wire

Connector Style Housing for female terminals

Mating Tab Width .64 mm [.025 in]

Sealable No

Centerline (Pitch) (in) .1

[↓ PRODUCT DRAWING](#)
English

[↓ 3D PDF](#)

DOCUMENTATION

Product Drawings

FEMALE CONNECTOR ASSEMBLY, 4 POSITION (1X4), UNSEALED, GENERATION Y

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Instruction Sheets

Instruction Sheet (U.S.)

Generation Y Unsealed Female Connectors

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector System Wire-to-Board, Wire-to-Device, Wire-to-Wire

Connector Style Housing for female terminals

Sealable No

Hybrid Connector No

Terminates To Wire & Cable

Primary Locking Feature Integrated in Housing

Strain Relief No

Row-to-Row Spacing 6 mm [.236 in]

Configuration Features

Number of Positions 4

Number of Rows 1

Body Features

Color Black

Cable Exit Angle 180°

Body Material PA GF

Contact Features

Mating Tab Width .64 mm [.025 in]

Mechanical Attachment

Mounting Feature No

Terminal Position Assurance Yes

Polarized Yes

Housing Features

Centerline (Pitch) (in) .1

Pitch (mm) 2.54

Dimensions

Width 13.4 mm [.528 in]
Height 13.5 mm [.531 in]
Length 20.2 mm [.795 in]

Usage Conditions

Operating Temperature Range -40 – 100 °C [-40 – 212 °F]
Operating Temperature (Max) (°C) 70, 75, 80, 85, 90, 100
Operating Temperature (Max) (°F) 158, 167, 176, 185, 194, 212

Operation/Application

Circuit Application Signal

Industry Standards

Degree of Protection Other

Packaging Features

Packaging Method Package
Packaging Quantity 1200

Other

Connector Position Assurance Capable Yes
Serviceable Yes

Statement of Compliance

Statement of Compliance

PDF