Littelfuse® | Carling Technologies®
A Littelfuse® Brand

RR/LRR-Series

Rounded Rocker Switches

PRODUCT WEBPAGE

request sample, configure part





The RR and LRR-Series round rocker switches feature a uniquely sculpted rocker design with electrical ratings of up to 12A 125VAC, 10A 250VAC and fit an industry standard cutout, making installation a snap. The lighted LRR-Series can be wired to accommodate dependent or independent, illumination, neon or incandescent lamps with red, green, amber or white translucent rockers. Standard or custom actuator legends are available.

1	6-12	125-250	6-28
Pole	Amps	VAC	VDC

Typical Applications

- Appliances
- Vacuum Cleaners
- Office Automation
- Commercial Food
- Audio Visual
- Test & Measurement

www.carlingtech.com 860.793.9281 sales@carlingtech.com

Downloaded from Arrow.com.

Tech Specs

Dielectric Strength

UL/CUL: 1000V-live to dead metal parts & opposite polarity

Electrical Life

50,000 cycles

Operating Temperature

32°F to 185°F (0°C to 85°C)

Ordering Scheme

Sample Part Number	RR	1	1	2	-	B	B	-	N	N
Selection		1	2	3	4		5	6	7	8

1. SERIES

RR Rocker **LRR** Lighted Rocker

2. CIRCUIT

1 On-None-Off
2 (On)-None-Off
3 On-None-(Off)
4 On-None-On
5 On-None-(On)
6 On-Off-On

3. RATING

1 [1] 10A, 125-250VAC; 12A 125 VAC
1/4 HP 125-250 VAC
3 6A, 28 VDC
4 12A, 12 VDC
5 12A, 6 VDC

4. TERMINATION

2 .187 Tab

Notes:
1 Rating Code "1" has UL and cUL approval.
2 Neon Lamps (125 or 250 Volts) not recommended with green or blue actuators.

Browse Standard Parts >

5. ACTUATOR COLOR

RR-Series (Non-Illuminated) Solid Color
B Black
W White
R Red
LRR-Series (Illuminated) Transparent Color
1 Amber
2 Red
3 Blue
4 Green
5 Clear

6. BASE COLOR

B Black
W White
R Red

7. LAMP VOLTAGE


N None
A 6V Incandescent
B 12V Incandescent
C 28V Incandescent
J [2] 125V Neon
K [2] 250V Neon


8. ROCKER FACE LEGEND

N No imprinting
A On-Off (vertical)
B On-Off (horizontal)
D I-O (horizontal)
E I-O (vertical)
F O (on rocker end)
G II-O-I (vertical)
H II-O-I (horizontal)
J Off-On (vertical)
K Off-On (horizontal)


Dimensional Specs

inches [millimeters]





RECOMMENDED PANEL OPENING



*Manufacturer reserves the right to change product specification without prior notice.

Downloaded from Arrow.com.