

CATALOGUE START

PRODUCT SEARCH

→

SITEMAP

TYPE

TXT

PHOTO

HELP

Mobile Catalogue

Industrial Components

Pressure switches

Electronic Pressure Switches

Electronic Pressure switch for gas, low viscosity liquid (SmartPress)

PST001RG12S-R

PST002AG12S-R

PST002RG12S-R

PST004RG12S-R

PST010AG12S-R

PST010RG12S-R

PST025RG12S-R

PST060RG12S-R

PST100RG12S-R

PST250RG12S-R

PST600RG12S-R

PSTM250RG12S-R

PSTM400RG12S-R

PSTM600RG12S-R

PSTV01RG12S-R

ST12-4-A

ST12-4-AK

ST12-4-GK

ST12-5-A

STA12

U430B

Documents for: PSTV01RG12S-R

Document type (Language)	File name	File size
TXT Product Description (English)	PSTV01RG12S-R	
Specification sheet (English)	en0b0346-ge51r0715.pdf	313 KB
Specification sheet (German)	ge0b0346-ge51r0715.pdf	316 KB
Specification sheet (Hungarian)	hu0b0346-ge51r0609.pdf	295 KB
Installation/mounting instruction (English)	mu1b01881-ge51r0715.pdf	630 KB
Installation/mounting instruction (German)	mu1b01882-ge51r0715.pdf	621 KB
Installation/mounting instruction (French)	mu1b01883-ge51r0715.pdf	658 KB
Installation/mounting instruction (Italian)	it1b0188-ge51r0803.pdf	886 KB
Installation/mounting instruction (Multilingual)	lt1b0188-ge51r0803.pdf	791 KB
Installation/mounting instruction (Hungarian)	hu1b-0188-ge51r0803.pdf	781 KB
Certificate (German)	gecepstr-ge51r0706.pdf	209 KB
Certificate (English)	gecepstr-ge51r0706.pdf	209 KB
Certificate (French)	gecepstr-ge51r0706.pdf	209 KB
Certificate (--)	gostventile-ge51r0316.pdf	540 KB

Terms and Conditions | Privacy Statement

Copyright Honeywell Inc. 2017

Downloaded from [Arrow.com](#).