

Ha-VIS RFID Antennas



LOCFIELD 2m al, 2.5m tl, Ø 3mm, SMA, FCC

LOCFIELD 2m al, 2.5m tl, Ø 3mm, SMA, FCC

Part number: 20 93 610 1200 10



Please [login](#) or [register](#) for a free MyHARTING Account to see all information about product availability and your order.

Technical data

Identification



Series	Ha-VIS LOCFIELD®
Element	Antenna

Connection data

Termination method	Direct coax cable (2.5 m) with SMA connector, diameter 3 mm
---------------------------	---

Technical characteristics

Operating temperature	-20 ... +65 °C
Storage temperature	-40 ... +85 °C
Degree of protection acc. to IEC 60529	IP65
Cable length	2.5 m
Cable diameter	3 mm
Frequency	902 ... 928 MHz
Impedance	50 Ω
Polarisation	Linear
Gain	-7 dBi
Opening angle	360 °
Transmitting power	2 W

Commercial data

Packaging size	1
Net weight	58 g
Country of origin	Germany
European customs tariff number	85291069



Accessories



Extension cable

Extension cable H 155 PVC, SMA m/f, 3m

20 93 204 0113

Extension cable

Extension cable H 155 PVC, SMA m/f, 1m

Exte

20 93 204 0112

Products frequently purchased together



Ruggedised UHF Ultra low range

RF-ANT-LR10

20 93 201 0303

Ha-VIS LOCFIELD®

LOCFIELD 1m al, 1.5m tl, Ø 3mm, SMA, FCC LOCFI

20 93 610 1200 20

HARTING contact: HARTING Inc. of N.America Bowes Road 1370 60123-5538 Elgin United Sta
HARTING support: 866-278-0306 E-mail address
(For questions regarding products, orders and user accounts)
Website support: E-mail address (For technical problems regarding the website)



© HARTING Technology Group

[Home](#) ` [Contact](#) ` [Privacy Policy](#) ` [Terms of Use](#) ` [Sales and delivery conditions](#) ` [Cookie policy](#) ` [Imprint](#)

