



Part Number : [2009150003](#)  
Product Description : MultiCat High-Power  
Circular Receptacle Housing, 3 Circuits, Black  
Series Number : 200915  
Status : Active  
Product Category : Connector Housings  
Engineering Number : FKB3W3S



Documents & Resources

Drawings


[2009150003\\_sd.pdf](#)  
[2009150003-PK.pdf](#)

Specifications

[2009140003-AS-000.pdf](#)  
[2009140003-000.pdf](#)  
[2009140003-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

## Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Connector Housings
Series	200915
Description	MultiCat High-Power Circular Receptacle Housing, 3 Circuits, Black
Application	Power, Wire-to-Wire
Product Name	MultiCat
UPC	889056746861

#### Agency

UL	E29179
----	--------

#### Physical

Circuits (maximum)	3
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	PEI
Net Weight	1.963/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No

Pitch - Mating Interface	6.83mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +150°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
MultiCat High-Power Circular Plug Housing, 3 Circuits, Black	<u>2009140003</u>

### Use with Part(s)

Description	Part Number
MultiCat High-Power Receptacle Terminals	<u>201846</u>

---

This document was generated on Apr 25, 2025