

4-Port Desktop KVM Switch (USB)

MODEL NUMBER: B006-VU4-R



Description

Tripp Lite's 4-port Desktop USB KVM Switch is the optimal solution for controlling up to 4 USB computers from one VGA monitor and USB keyboard/mouse. Manually switch between connected computers using pushbuttons or hotkey controls; or, monitor connected computers automatically via Auto Scan Mode. The B006-VU4-R is operating system independent, and works with all computers that have an available VGA and USB port. It supports video resolutions up to 2048 x 1536, and features a compact design that does not require software or complicated set-up procedures. Constructed of heavy-duty steel housing. Order P758 Cables separately.

Features

- Control up to 4 USB computers from a single VGA monitor and USB keyboard/mouse
- Order P758 Cables separately
- Port LEDs illuminate Dim Orange to indicate a computer is connected, and Bright Orange to indicate it is the selected port
- Supports video resolutions up to 2048 x 1536, DDC2B
- No software or complicated set-up procedures required
- Manually switch between connected computers via front panel pushbuttons or hotkey commands
- Automatically monitor connected computers via Auto Scan Mode
- Compatible with all major operating systems
- Compatible with most mice; including scroll mice
- Constructed of heavy-duty steel housing

Specifications

OVERVIEW	
UPC Code	037332152947
Console	No
Max CPU	4

Highlights

- Control up to 4 USB computers from a single VGA monitor and USB keyboard/mouse
- Switch between connected computers via pushbuttons or hotkey commands
- Auto Scan Mode allows monitoring of connected computers without manually switching between them
- Compatible with all major operating systems
- Supports video resolutions up to 2048 x 1536, DDC2B

Package Includes

- B006-VU4-R 4-port USB KVM Switch
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A / Output: 5.3V, 2.4A)
- Owner's manual

Technology	VGA/SVGA
VIDEO	
Max Supported Video Resolution	2048 X 1536, DDC2B
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.5A
AC Power Adapter Output Specs (V / A)	5.3V / 2.4A
AC Power Adapter Cord Length (ft.)	5
AC Power Adapter Cord Length (m)	1.5
POWER	
Power Source Type	AC Adapter
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Online Selected (Orange)
PHYSICAL	
LCD Monitor (cm)	Not Applicable
Shipping Dimensions (hwd / in.)	3.50 x 9.80 x 8.70
Shipping Dimensions (hwd / cm)	8.89 x 24.89 x 22.10
Shipping Weight (lbs.)	2.20
Shipping Weight (kg)	1.00
Unit Dimensions (hwd / in.)	1.700 x 7.900 x 2.900
Unit Dimensions (hwd / cm)	4.32 x 20.07 x 7.37
Unit Weight (lbs.)	1.50
Unit Weight (kg)	0.68
ENVIRONMENTAL	
BTUs	7.1694 BTU/Hr
COMMUNICATIONS	
Port Control	Push Buttons, Hotkeys
IP Remote Access	No
CONNECTIONS	

Number of Ports	4
PC/Server Connections	USB; VGA
Side A - Connector 1	(4) HD15 (MALE)
Side A - Connector 2	(4) USB B (FEMALE)
Side B - Connector 1	(1) HD15 (FEMALE)
Side B - Connector 2	(2) USB A (FEMALE)
Computer Keyboard and Mouse Interface	USB
Computer Monitor Interface	VGA
Console Keyboard and Mouse Interface	USB
Console Monitor Interface	VGA
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Cat5 KVM Switch	No
NIAP-Certified Secure	No
Number of Users	1
Autoscan (Y,N)	Y
Autoscan Duration	11 TO 99 SECONDS; USER-DEFINEABLE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty