



Part Number : [351500209](#)

Product Description : VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 2 Circuits, Natural, Glow-Wire Capable

Series Number : 35150

Status : Active

Product Category : Connector Housings

Documents and Resources

Drawings

[351500209 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[351500000AS ENG-000.pdf](#)

[351500000AS KOR-000.pdf](#)

[PK-35150-002-001.pdf](#)

[PS-35150-003-001.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS |  per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|--------------|---|
| Status | Active |
| Category | Connector Housings |
| Series | 35150 |
| Description | VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 2 Circuits, Natural, Glow-Wire Capable |
| Application | Power, Wire-to-Wire |
| Product Name | VersaBlade |
| UPC | 756054256411 |

Agency

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

Physical

| | |
|--------------------|------------|
| Circuits (maximum) | 2 |
| Color - Resin | Natural |
| Gender | Receptacle |
| Glow-Wire Capable | Yes |

| | |
|-------------------------------|----------------|
| Keying to Mating Part | No |
| Lock to Mating Part | Yes |
| Material - Resin | PET/PC |
| Net Weight | 1.706/g |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 6.20mm |
| Pitch - Termination Interface | 6.20mm |
| Polarized to Mating Part | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +110°C |

Mates With / Use With

Mates with Part(s)

| Description | Part Number |
|---------------------------------|-----------------------|
| VersaBlade Hybrid Plug Housings | 35151 |

Use with Part(s)

| Description | Part Number |
|--|---------------------------|
| VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Natural | 351500290 |
| VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Red | 351500292 |
| VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Yellow | 351500293 |
| VersaBlade Terminal Position Assurance (TPA) Retainer, 6.20mm Pitch, 2 Circuits, Blue | 351500294 |
| VersaBlade Male Crimp Terminals | 35745 |