



**Part Number :** [1301430143](#)

**Product Description :** Watertite Extreme Cordset 16 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 15.24m (50.0'), NEMA 5-15, 125V

**Series Number :** 130143

**Status :** Active

**Product Category :** Wiring Devices

**Engineering Part Number :** 14W47B163



---

## Documents and Resources


### Drawings

[1301430143 sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

Status	Active
Category	Wiring Devices
Series	130143
Description	Watertite Extreme Cordset 16 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 15.24m (50.0'), NEMA 5-15, 125V
IP Rating	IP67
NEMA Configuration	NEMA 5-15
Product Name	Watertite Extreme
Specialty	N/A
Type	Cordset
UPC	78678879660

#### Agency

CSA	LR6837
UL	E38085

#### Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	125V

#### Physical

Cord Grip Body Size	F2 1/2"
Cord Type	16/3 SOOW
Flange	No
Flip Lid	No
Gender	Male-Female

Length	15.24m (50.0')
Lighted Connector	No
Locking Blade	No
Net Weight	777.000/g
Poles	2-pole/3-wire
Receptacle Type	Single

---

This document was generated on May 27, 2026