



Part Number : [1301460125](#)
Product Description : Watertite Extreme Duplex
Receptacle with Flip Coverplate, 2 Pole/3 Wire, NEMA
5-20, 125V
Series Number : 130146
Status : Active
Product Category : Wiring Devices
Engineering Number : 60W33DPLX



Documents & Resources

Drawings

[1301460125 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extreme Duplex Receptacle with Flip Coverplate, 2 Pole/3 Wire, NEMA 5-20, 125V
IP Rating	IP67
NEMA Configuration	NEMA 5-20
Product Name	Watertite Extreme
Specialty	N/A
Type	Receptacle
UPC	78678871432

Agency

CSA	LR6837
UL	E68122

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	125V

Physical

Cord Type	N/A
Flange	No

Flip Lid	Yes
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	No
Net Weight	1.000/g
Poles	2-pole/3-wire
Receptacle Type	Duplex

This document was generated on Oct 04, 2025