HellermannTyton

Specification Sheet

Part Number: CTAM20C2



Suitable for applications with minimal space.

CTAM has 4-way entry design for use in line or at 90° angle to cable run.

CTAM mounts are available in different sizes and materials.

Cable Tie Anchor Mount, 0.20" Hole Dia, 0.20" Max Tie Width, PA66, Black, 100/pkg

Article Number	151-31201
Type	CTAM2
Color	Black (BK)
Quantity Per	pack
Product Description	Anchor Mounts for cable ties are suitable for applications with minimal space. Anchors are mounted onto the equipment prior to cable installation and take up no more space than the cable itself. Choose between a four-way entry design that can be used either 'in line' or at 90 degrees to the cable run.
Short Description	Cable Tie Anchor Mount, 0.20" Hole Dia, 0.20" Max Tie Width, PA66, Black, 100/pkg
Global Part Name	CTAM2-PA66-BK

Downloaded from Arrow.com.

Length L (Imperial)	0.8
Length L (Metric)	20.4
Fixation Method	Screw Mount
Width W (Imperial)	0.4
Width W (Metric)	10.2
Cable Ties	T18 - T50
Height H (Imperial)	.20
Height H (Metric)	5.10
Cable Tie Width Max (Imperial)	0.2
Cable Tie Width Max (Metric)	5.0
Mounting Hole Diameter D (Imperial)	0.2 "
Mounting Hole Diameter D (Metric)	5.2 mm
Mounting Hole Diameter D Max (Metric)	5.2

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66

Downloaded from Arrow.com.

Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

Downloaded from Arrow.com.