







P	LTR	DESCRIPTION	DATE	DWN	APV
	A	RELEASE	28. JUL '15	SM	HG




Interface Drawing



M4 tapping x2

—This surface must be clean (water proof area),
Roughness ; Ra1.6



SECTION A-A


NOTE

1. APPLIED FEMALE CONNECTOR P/NO : 5-1419168-8
2. GENERAL TOLERANCE : ± 0.3
3. APPLICABLE CONTACT P/NO :

NO	P/NO	DESCRIPTION	WIRE SIZE
1	928918	.025 SEALED TAB	0.2-0.5mm ²
2	963716	.025 SEALED TAB	0.5-0.75mm ²

4. APPLIED BOLT TORQUE : MAX 0.2kgf · m
M4*12 SCREW WITH WASHER.

2	RED	SILICON	INNER SEAL	I
1	BLACK	PBT-GF15	CAP HSG	I
NO	COLOR	MATERIAL	DESCRIPTION	Q' T

control priority dimension ;		2	RED	SILICON	INNEL SEAL	1
■ CRITICAL, ☑ MAJOR, □ MINOR		1	BLACK	PBT-GFI5	CAP HSG	1
THIS DRAWING IS A CONTROLLED DOCUMENT.		NO	COLOR	MATERIAL	DESCRIPTION	Q' T
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.1 2 PLC ±0.01 3 PLC ±0.001 4 PLC ±0.0001 ANGLES ±		DWN SM LEE CHK KT LIM APVD HG CHO PRODUCT SPEC APPLICATION SPEC WEIGHT		
MATERIAL -		FINISH -		NAME 025 16P SEALED CAP ASS'Y		
				SIZE	CAGE CODE	DRAWING NO
				A3	00779	©-2219192
				RESTRICTED T		
CUSTOMER DRAWING				SCALE	SHEET OF	REV
						A