


Telescopic Slide Universal, 1 U, 457L

CATALOG NUMBER

20110-092



Universal Telescopic Slide with > 100 % extension and up to 39 kg load capacity.

CERTIFICATIONS



FEATURES

Lateral mounting on the 19" uprights (19" plane remains free for fixing the extension/drawer)

Static load-carrying capacity per pair 23 - 39 kg

Can be removed

Extension length > 100 %

Rail width $k = 9.7$ mm, max. installation width of extension/drawer $w = 429$ mm

PRODUCT ATTRIBUTES

Package Quantity: 2
Finish: Zinc Plated
Material: Steel
Product Family: MultipacPRO
Product Type: Telescopic Slide
Type: Universal
Net Weight: 1.35kg

ADDITIONAL PRODUCT DETAILS

Universal telescopic Rails can also be fitted without additional components in non-standard applications, this also in other than 19" cabinets.

To mount on 19" plane please order assembly kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America	Europe	Asia	Middle East & India
All locations	Straubenhardt, Germany	Shanghai, China	Dubai, United Arab Emirates
+1.763.422.2661	+49.7082.794.0	+86.21.2412.6943	+971.4.378.1700
Chat with us:	Betschdorf, France	Qingdao, China	Bangalore, India
nvent.com/schroff	+33.3.88.90.64.90	+86.532.8771.6101	+91.80.6715.2001
	Warsaw, Poland	Singapore	Istanbul, Turkey
	+48.22.209.98.35	+65.6768.5800	+90.216.250.7374
	Assago, Italy	Shin-Yokohama, Japan	Chat with us:
	+39.02.932.7141	+81.45.476.0271	nvent.com/schroff
	Chat with us:	Chat with us:	
	nvent.com/schroff	nvent.com/schroff	



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE