

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




FACEPLATE



PANDUIT P/N	WEIGHT
UICFPRTR4**	1.55 LB/10 PCS (704.0 g/10 PCS)

NOTES:
1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN [ ] ARE IN METRIC.
4. PART INCLUDES:
   - 1- FACEPLATE
   - 1- TAMPER RESISTANT COVER
   - 1- CLEAR SCREW COVER
   - 1- COLOR COORDINATED SCREW COVER
   - 2- CLEAR LABEL COVER
   - 2- MOUNTING SCREW
   - 2- 30° SLOPED RECESSED 1/2 INSERT (CHSRE2**)
   - 1- TAMPER RESISTANT SCREW FOR COVER
   - 1- PHILLIPS HEAD SCREW FOR COVER
5. MOUNTING RECOMMENDATIONS:
   - MOUNT TO MWBA1 (OR EQUIVALENT) SINGLE GANG WALL BOARD ADAPTER
   - IF IN-WALL BOX IS USED, DEPTH MUST BE MIN. OF 2.125[53.98] (FOR COPPER APPLICATIONS)



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	5/22/14	JSP	REFR	MMR	A. REVISED DRAWING TITLE BLOCK.	01340-07
R	7-24-02	JSP	MJD	MJD	RELEASED TO PRODUCTION	01340-07

PART NUMBER: UICFPRTR4**

TITLE: MINI-COM 4 POSITION ULTIMATE ID RECESSED FACEPLATE KIT WITH TAMPER RESISTANT COVER

CUSTOMER DRAWING

ITEM REVISION NAME: M01340AF/04

DATASET FILE NAME: M01340AF_DC/04B

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]
.X ± .XXX ± .010 [.3]
.XX ± .03[.8] ANGLES ±
THIRD ANGLE PROJECTION

MATERIAL: ABS

DRAWING NUMBER: 01340-07

DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
JSP	7-24-02	MJD	NONE		A

D1010ODA/14

Downloaded from Arrow.com.